

[See all 12 Products in Family](#)

**TECHSPEC® 20.0mm Dia x 3mm Thick 532/1064nm, Zerodur Dual Band Laser Mirror**



Stock #29-058 **8 In Stock**

⊖ 1 ⊕ **\$270<sup>.20</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>\$270.20</b> each
Qty 6-25	<b>\$238.00</b> each
Qty 26-49	<b>\$212.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

3.00 ±0.20 **Thickness (mm):**

20.00 +0.00/-0.20 **Diameter (mm):**

90 **Clear Aperture (%)**:

30 **Parallelism (arcsec)**:

Commercial Polish **Back Surface:**

Protective as needed **Bevel:**

Ground **Edges:**

## Optical Properties

ZERODUR® **Substrate:**

20-10 **Surface Quality:**

Laser Mirror (532, 1064nm) **Coating:**

532, 1064 **Design Wavelength DWL (nm):**

Rabs >99.5% @ 532 & 1064nm **Coating Specification:**

Dielectric **Coating Type:**

15 J/cm<sup>2</sup> @ 20ns @ 532nm 20 J/cm<sup>2</sup> @ 20ns @ 1064nm **Damage Threshold, By Design:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- >99.5% Reflectivity at Design Wavelengths
- Low Coefficient of Thermal Expansion
- 532/1064nm or 635/670/1064nm Wavelength Bands

TECHSPEC® Zerodur® Dual Band Laser Line Mirrors feature high reflectivity coatings with either two or three wavelength bands on a durable Zerodur® substrates. The ZERODUR® substrates have a low coefficient of thermal expansion (CTE) of  $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$ , which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® Zerodur® Dual Band Laser Line Mirrors are available in a highly reflective 532/1064nm or 635/670/1064nm dual band coatings and multiple standard diameter options for Nd:YAG lasers and red and green guide beams. These mirrors are ideal for beam steering applications in both laboratory and OEM laser systems.