


**TECHSPEC® 25mm Dia. 2.0° Beam Dev. Fused Silica Wedge Prism Uncoated**



TECHSPEC Fused Silica Wedge Prisms

Stock **#84-862** [CONTACT US](#)

⊖ 1 ⊕ **\$\$192<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>\$\$192.66</b> each
Qty 6-25	<b>\$\$153.83</b> each
Qty 26-49	<b>\$\$144.12</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**SPECIFICATIONS**

**General**

Wedge Prism

Type:

Note:

Specify this is S1 & S2 power and irregularity, not the overall power of the wedge

## Physical & Mechanical Properties

25.00 +0.00/-0.10 **Diameter (mm):**

3.00 **Thickness (mm):**

Protective as needed **Bevel:**

4° 11'14" **Wedge Angle (arcmin):**

## Optical Properties

15 **Angle Tolerance (arcsec):**

Uncoated **Coating:**

355 **Design Wavelength DWL (nm):**

**Fused Silica** (Corning 7980) **Substrate:**

20-10 **Surface Quality:**

Beam Deviation **Image Orientation:**

200 - 2200 **Wavelength Range (nm):**

0.50 **Power (fringes) @ 632.8nm:**

0.20 **Irregularity (fringes) @ 632.8nm:**

2.00 **Ray Deviation @ 355nm (°):**

3.49 **Power (diopters):**

4.19° **Wedge Angle (°):**

## Material Properties

0.52 **Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 219:**

**View** **Certificate of Conformance:**



## PRODUCT DETAILS

- Deviates Laser Beam Path from 0.5° - 5.0°
- Ideal for UV to NIR Beam Steering Applications from 250 to 1064nm
- Ideal for High Power Beam Steering Applications

TECHSPEC® Fused Silica Wedge Prisms are designed for a range of laser beam steering applications requiring UV-Vis or first through fourth Nd:YAG harmonic Anti-Reflection Coatings. They are optimized to ensure the highest level of system performance using tightly controlled specifications including  $\lambda/10$  surface flatness, 20-10 surface quality, and a wedge tolerance of 15 or 30 arcseconds. The Nd:YAG coated versions feature high transmittance and guaranteed laser damage thresholds specific to the design wavelength. TECHSPEC® Fused Silica Wedge Prisms utilize a wedge design to deviate laser beam path from 0.5° – 5°. By creating a risley prism pair using two wedge prisms with the same ray deviation, custom beam steering up to two times the wedge deviation is possible. A low coefficient of thermal expansion ensures accurate beam steering in high power laser applications.

**Note:** Power Diopter is defined as 1cm deviation at a distance of 1m from the prism. TECHSPEC® Wedge Prisms are also available in [N-BK7 versions](#).

## TECHNICAL INFORMATION



## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).