

TECHSPEC[®] 20mm, 632.8nm, Lateral Displacement Polarizing Beamsplitter



Lateral Displacement Beamsplitters

Stock **#47-191** 1 In Stock

-

1

+

S\$1,120⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$1,120.00 each
Qty 6-25	S\$889.00 each
Qty 26-99	S\$826.00 each
Need More?	Request Quote

Product Downloads

General	
Linear Polarizer	Type:
Polarizing	Type of Optics:
Physical & Mechanical Properties	
80.00	Clear Aperture (%):


Prism	Construction:
±0.1	Dimensional Tolerance (mm):
<2	Parallelism (arcmin):
Optical Properties	
±5	Angle Tolerance (arcsec):
20.00	Beam Separation (mm):
R _{abs} <0.3% @ 632.8nm	Coating Specification:
632.8	Design Wavelength DWL (nm):
>1000:1	Extinction Ratio:
>95	P-Polarization Transmission (%):
>99	S-Polarization Reflection (%):
N-BK7	Substrate: ☐
λ/8	Surface Flatness (P-V):
40-20	Surface Quality:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Visible and NIR Coating Options Offered
- Simplifies Benchtop Layout
- Split Incident Beam into Two Displaced Parallel Beams

TECHSPEC® Lateral Displacement Beamsplitters output two parallel beams separated by a fixed distance. The beamsplitters consist of a precision **rhomboid prism** cemented to a $\lambda/8$ **right angle prism**. The high tolerance design ensures the exiting beams are parallel to within 2 arcmin. TECHSPEC® Lateral Displacement Beamsplitters' entrance and exit faces feature a multi-layer anti-reflection (AR) coating for increased efficiency. Polarizing and non-polarizing coatings are available for these beamsplitters.

Technical Information



Size (A)	10mm	20mm
Beam Separation	10mm	20mm

