

[See all 23 Products in Family](#)

## 20mm Dia. Left-Handed Plastic Circular Polarizer (CP42HE)



Stock **#88-096** **7 In Stock**

S\$46<sup>.90</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$46.90</b> each
Qty 6-25	<b>S\$39.20</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Left-Handed Circular Polarizer **Type:**

#### Physical & Mechanical Properties

20.00 +0.0/-0.3 **Diameter (mm):**

2.29 ±0.24 **Thickness (mm):**

Circular Plastic (PMMA) Circular Polarizers **Construction:**

## Optical Properties

<a href="#">CP42HE on PMMA</a>	<b>Substrate:</b> <input type="checkbox"/>
42	<b>Transmission (%):</b>
400 - 700	<b>Wavelength Range (nm):</b>
>99.90	<b>Polarization Efficiency (%):</b>

## Environmental & Durability Factors

-40 to +80	<b>Operating Temperature (°C):</b>
80 x 500	<b>Heat Resistance (°C x Hours):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 235:</b>

## Product Details

- Greater than 42% Transmission
- Available with Film or Plastic Substrate
- Right-Handed or Left-Handed Designs Available

Circular Polarizers (CP42HE and CP42HER) are ideal for reducing glare in a variety of imaging applications or for increasing the visibility of displays in bright environments. These circular polarizers feature excellent transmission of visible light from 400 – 700nm. The plastic substrate offers increased durability, while the film substrate offers increased flexibility and can be cut to fit an application's needs. Circular Polarizers (CP42HE and CP42HER) have Left-handed (CP42HE) and right-handed (CP42HER) polarization directions available. The best performance will be achieved at 560nm and polarization may become more elliptical the further the deviation from this recommended wavelength.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a Circular Polarizer (CP42HE and CP42HER) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.