

**TECHSPEC® 20mm N-SF11 Uncoated Equilateral Prism**



Equilateral Prisms

Stock **#49-431** **20+ In Stock**

⊖ 1 ⊕ **S\$187<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$187.60</b> each
Qty 6-25	<b>S\$149.80</b> each
Qty 26-49	<b>S\$140.70</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Equilateral Prism **Type:**

**Physical & Mechanical Properties**

20.00 **Length of Face (mm):**

20.00 **Length (mm):**

Dimensional Tolerance (mm):

±0.1

## Optical Properties

Uncoated

Coating:

[N-SF11](#)

Substrate:

40-20

Surface Quality:

±2

Angle Tolerance (arcmin):

Dispersion

Image Orientation:

400 - 2500

Wavelength Range (nm):

2.50

Power (fringes) @ 632.8nm:

0.50

Irregularity (fringes) @ 632.8nm:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Ideal for Light Dispersion
- Sizes Ranging from 5 - 50mm
- Available Uncoated or Anti-Reflection Coated
- Additional [Equilateral Prism](#) Options Available

TECHSPEC® Equilateral Prisms feature three equal 60° angles and are often referred to as dispersing prisms. Equilateral prisms are ideal for wavelength separating applications and light dispersion. These prisms are available in sizes ranging from 5-50mm. Our TECHSPEC® Equilateral Prisms are offered uncoated or with a single layer MgF2 anti-reflection coating. Additional [Equilateral Prism](#) options are available.

## Technical Information

