

[See all 18 Products in Family](#)

TECHSPEC® 20mm Protected Silver, N/20 Fused Silica Right Angle Prism Mirror



Stock #22-555 [CONTACT US](#)

⊖ 1 ⊕ **\$372⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	\$372.40 each
Qty 6-25	\$299.60 each
Qty 26-49	\$281.40 each
Need More?	Request Quote

Product Downloads

General

Right Angle Mirror **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

25.45 x 18.00 **Clear Aperture CA (mm):**

+0.00/-0.10	Dimensional Tolerance (mm):
28.30	Length of Hypotenuse (mm):
20.00	Length of Legs (mm):
Optical Properties	
0.45 - 10	Wavelength Range (µm):
Metal	Coating Type:
Protected Silver (450-10000nm)	Coating:
λ/20	Surface Flatness (P-V):
450 - 10000	Wavelength Range (nm):
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Coating Specification:
20-10	Surface Quality:
0.5 J/cm ² @ 532nm & 1064nm, 10ns	Damage Threshold, Reference: <input type="checkbox"/>
±15	Angle Tolerance (arcsec):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Precision Fused Silica Substrates for Increased Thermal Stability
- Ideal for System Alignment
- Enhanced Aluminum, Protected Gold, and Protected Silver Coatings Available

TECHSPEC® λ/20 Fused Silica Right Angle Prism Mirrors feature broadband metal coatings and a ±15 arcsecond angular tolerance for applications that require precision alignment. These highly reflective right angle mirrors simplify alignment when mounting and are easily integrated into systems that redirect light at 90°. TECHSPEC® λ/20 Fused Silica Right Angle Prism Mirrors utilize Fused Silica substrates for high temperature environments and their precision design and tolerances enable easy system integration. Coating options feature >95% reflectivity from 450nm to the long wave infrared (IR).

Technical Information



Image above shows light reflecting off the coated hypotenuse.



Coating Curves

;