

## 20µm Aperture Diameter, Mounted, Precision Pinhole



20µm Aperture Diameter, Mounted, Precision Pinhole, #56-279

Stock **#56-279** 3 In Stock

-

1

+

S\$117<sup>60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | S\$117.60 each                |
| Qty 6-10       | S\$103.88 each                |
| Qty 11+        | S\$96.04 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                      |
|----------------------------------|----------------------|
| Mounted                          | Type:                |
| Physical & Mechanical Properties |                      |
| 25 +0.4/-0.000                   | Outer Diameter (mm): |
| Stainless Steel                  | Construction:        |

|              |                               |
|--------------|-------------------------------|
| 20           | Fixed Aperture Diameter (µm): |
| 0.01 Nominal | Thickness (mm):               |
| ±5           | Aperture Tolerance (µm):      |
| ±125         | Aperture Centration (µm):     |

Threading & Mounting

|            |                       |
|------------|-----------------------|
| 1.25 ±0.05 | Mount Thickness (mm): |
|------------|-----------------------|

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 247:                  |

## Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- [High Power Apertures](#) Available

### Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to ±0.002" (50 microns). They are constructed of stainless steel and are 3/8" (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

### Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

**Note:** Aperture Centering to Mount ±125 microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

## Technical Information

