

## 20W Tungsten Lamp



20W Tungsten Lamp (Front), #87-299



Stock **#87-299** **1 In Stock**

- 1 + **\$2,765<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>\$2,765.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**  
External power supply and AC cord included. Fiber patchcord listed under Accessories tab sold separately.

**Lamp Lifetime (hours):**  
2000

### Physical & Mechanical Properties

**Dimensions (mm):**

121 x80 x67

## Optical Properties

350 - 2600 **Wavelength Range (nm):**

## Electrical

20.00 **Output Power (W):**

## Hardware & Interface Connectivity

SMA-905 **Connector:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Designed for Use with [Spectrometers](#)
- Lamps Available for UV to NIR
- Xenon, Tungsten, or Deuterium Sources

Broadband Fiber-Coupled Light Sources are ideal for use in a variety of spectroscopy applications and for coupling with the Fiber Optic Reflectance Sphere. The pulsed Xenon source is designed for applications from the UV to visible. The Tungsten source is designed for applications in the visible to NIR. The Deuterium/Tungsten source is ideal for applications requiring wide spectral ranges from the UV to NIR.