

2.0X, High Resolution Inline Telecentric Lens



Stock #65-028 3-5 DAYS



1



S\$5,046.00

ADD TO CART

Qty 1+
S\$5,046.00

Volume Pricing
Request Quote

Get Product Downloads

Horizontal Field of View, 2/3" Sensor:
4.4mm

Numerical Aperture NA, Object Side:
0.13

Resolving Power, Image Space (μm):
5.70

Working Distance Tolerance (mm):
±1.00

Note:
Magnification Tolerance %: ±3

Type: Telecentric Lens
Primary Magnification PMAG: 2X
Maximum Sensor Format: 2/3"
Working Distance (mm): 100.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/8 - Closed
Distortion (%): ≤0.05
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View