

TECHSPEC[®] 22mm CA, 125mm FL, Mounted MgF₂ Coated Plano-Convex Lens



Mounted MgF₂ Coated Plano-Convex (PCX) Lenses



Stock #13-001 CLEARANCE 3-5 DAYS

-

1

+

S\$89.83

ADD TO CART

Qty 1+

S\$89.83

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
125.00

Substrate: ☐
[N-BK7](#)

f#:
5

Numerical Aperture NA: 0.10
Coating: MgF ₂ (400-700nm)
Type: Plano-Convex Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL from Housing (mm): 122.7
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 22.0
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Edge Thickness ET (mm): 2.28
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): 64.62
Surface Quality: 40-20
Lens Included: #32-862
Mount Included: #56-353
Mount Diameter (mm): 30.0
Extension Length (mm): 16.3
Total Length (mm): 20.3
Thread Type: C-Mount
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View