

20mm Diameter Laser Diode Mirror



Stock **#46-619** **20+ In Stock**

- 1 + S\$41^{.65}

ADD TO CART

Volume Pricing

Qty 1-10	S\$41.65 each
Qty 11-24	S\$32.20 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

20.00 ±0.25 **Diameter (mm):**

3.00 **Thickness (mm):**

±0.25 **Dimensional Tolerance (mm):**

Optical Properties

Dielectric **Coating Type:**

Dielectric Mirror (500-700nm) **Coating:**

633 **Design Wavelength DWL (nm):**

Float Glass **Substrate:**

$R_{\text{abs}} > 97\%$ @ 633nm **Coating Specification:**

80-50 **Surface Quality:**

Environmental & Durability Factors

ML-C-48497A **Durability:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**


Product Details

- Over 95% Reflectance of Visible Laser Diode Light
- Ideal for Multiple Reflection Systems
- Coating Optimized for 633nm at 45° AOI

Visible Laser Diode Mirrors are specially coated to attain maximum reflection of visible laser diodes. Optimized for 633nm at a 45° angle of incidence, these mirrors provide 97% reflectance versus only 85 - 90% for standard first surface mirrors. This reduced loss is particularly important in multiple reflection systems, where loss can significantly impact system efficiency. Visible Laser Diode Mirrors feature a float glass substrate and are ideal for multiple reflection systems.

Technical Information

Visible Laser Diode Mirror Reflectance at 45°



@ 500nm	95.0%
@ 550nm	97.0%
@ 600nm	97.5%
@ 633nm	97.0%
@ 635nm	97.0%
@ 650nm	96.5%
@ 670nm	96.0%
@ 675nm	95.0%
@ 700nm	94.5%

[Quote Your Size](#)

[Compatible Mounts](#)