

TECHSPEC® 20X, 0.19 NA, UCf Objective



Stock #26-690 **16 In Stock**

⊖ 1 ⊕ **S\$512⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-2	S\$512.40 each
Qty 3-4	S\$477.40 each
Qty 5-9	S\$460.60 each
Need More?	Request Quote

Product Downloads

General

Fluorite **Type:**

Finite Conjugate **Style:**

Edmund Optics® **Manufacturer:**

Physical & Mechanical Properties

158.51 Length (mm):

29 Maximum Diameter (mm):

139 Weight (g):

Optical Properties

0.44 Horizontal Field of View, 2/3" Sensor:

0.704 Horizontal Field of View, 1.1" Sensor:

8.00 Focal Length FL (mm):

20X Magnification:

0.19 Numerical Aperture NA:

3.51 Resolving Power (μm):

7.42 Depth of Field (μm):

7.7 Working Distance (mm):

400 - 700 Wavelength Range (nm):

17.6 Field Number (mm):

Sensor

1.1" Maximum Sensor Format:

Threading & Mounting

C-Mount Mounting Threads:

Environmental & Durability Factors

+10 to +40 Operating Temperature ($^{\circ}\text{C}$):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Compact Finite Conjugate Objectives
- Mount Directly to a C-Mount Camera
- Near Diffraction Limited performance

TECHSPEC® UCf Objective Series are compact objectives that are finite conjugate by design, but achieve similar imaging performance of infinity corrected objectives and do not require a secondary tube lens to generate an image on the sensor. Available at 2X, 4X, 5X, 10X, 15X, and 20X magnifications. These objectives mount directly to a C-mount camera without additional extension tubes.