

TECHSPEC® 21 x 30mm Protected Gold, λ/4 Mirror



Stock **#32-742** 3-5 DAYS

- 1 + **S\$105.13**

ADD TO CART

Qty 1-5
S\$105.13
Qty 6+
S\$84.10
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: □
BOROFLOAT®

Back Surface:
Ground

Surface Quality:

60-40
Dimensions (mm): 21.0 x 30.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Length (mm): 30.00
Width (mm): 21.00
Damage Threshold, Reference:  0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant