

248.6nm High Performance Laser Line Filter 12.5mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#12-258** [CONTACT US](#)

-

1

+

S\$623⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$623.00 each
Need More?	Request Quote

Product Downloads

General

Bandpass Filter

Type:

Physical & Mechanical Properties

12.50 +0.0/-0.1

Diameter (mm):

≥10

Clear Aperture CA (mm):

±0.10

Thickness Tolerance (mm):

Construction:	
Mounted in Black Anodized Ring	
Physical Durability:	
ML-C-48497AParagraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	
Substrate Thickness (mm):	
2.0 ±0.1	
Optical Properties	
Angle of Incidence (°):	
0 ±2	
Bandwidth (nm):	
1.7	
OD 5 Blocking Wavelength Range (nm) :	
228.2 - 246.1 & 251.1 - 279.9	
OD 6 Blocking Wavelength Range (nm):	
228.7 - 244.9 & 252.3 - 273.5	
Optical Density OD (Average):	
≥6.0	
Center Wavelength CWL (nm):	
248.60	
Design Wavelength DWL (nm):	
248.6	
Full Width-Half Max FWHM (nm):	
1.70 - 2.2	
Substrate: 	
Fused Silica	
Minimum Transmission (%):	
>40	
Coating:	
Hard Coated	
Surface Quality:	
60-40	
Transmission (%):	
>40	
Blocking Wavelength Range (nm):	
228.2 - 246.1 & 251.1 - 279.9	
Threading & Mounting	
Mount Thickness (mm):	
3.5 ±0.1	
Environmental & Durability Factors	
Environmental Durability:	
ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 209:	
Compliant	
Certificate of Conformance:	
View	







Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts