

TECHSPEC® 25 x 38mm 30R/70T, VIS Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock #48-392 3-5 DAYS

⊖ 1 ⊕ **S\$236.35**

ADD TO CART

Qty 1-5

S\$236.35

Qty 6+

S\$188.50

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):

45

Clear Aperture (%):

>85

Coating Specification:

Surface 1: 30/70 ±5% @550nm, ±10% @400 -

700nm
Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 400 - 700nm

Construction:
Plate

Dimensions (mm):
25.0 x 38.0 +0.0/-0.25

Edges:
Cut with 0.25mm maximum edge chip

Note:
Beamsplitter-coated side is marked with a black dot

Parallelism (arcmin):
 ≤ 3

Reflection/Transmission Ratio (R/T):
30/70

Substrate:
[N-BK7](#)

Surface Flatness (P-V):
1 λ per inch

Surface Quality:
60-40

Thickness (mm):
3.00 \pm 0.25

Type:
Standard Beamsplitter

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)
