

[See all 102 Products in Family](#)

TECHSPEC[®] 25.0mm Diameter x 150.0mm FL, 1550nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#84-262** 1 In Stock

☐ [Other Coating Options](#)

-

1

+

S\$82⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$82.60 each
Qty 10-25	S\$74.90 each
Qty 26-49	S\$66.15 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.0/-0.025	
Centering (arcmin): <1	
Center Thickness CT (mm): 3.50 ±0.10	
Edge Thickness ET (mm): 2.49	
Clear Aperture CA (mm): 24	
Bevel: Protective as needed	

Optical Properties	
Effective Focal Length EFL (mm): 150.00 @587.6nm	
Back Focal Length BFL (mm): 147.75	
Coating: Laser V-Coat (1550nm)	
Coating Specification: R _{abs} <0.25% @ 1550nm	
Substrate: N-BK7	
Surface Quality: 40-20	
Power (P-V) @ 632.8nm: 1.5λ	
Irregularity (P-V) @ 632.8nm: λ/4	
Focal Length Tolerance (%): ±1	
Radius R₁ (mm): 77.55	
f##: 6.00	
Numerical Aperture NA: 0.08	
Design Wavelength DWL (nm): 1550	
Damage Threshold, By Design: 5 J/cm² @ 1550nm, 10ns	

Regulatory Compliance	
RoHS 2015: Compliant	
Certificate of Conformance: View	
Reach 235: Compliant	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- <0.25% Reflection at Design Wavelength
- Coatings Available for Diode, HeNe, and Nd:YAG Laser Sources
- BBAR Coating Options Also Available: [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and 1550nm V-Coated Options Offered

TECHSPEC® 1550nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 1550nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [633nm](#), [785nm](#), [980nm](#), and [1064nm](#). Other coating options are available, including [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).



Technical Information



Compatible Mounts