

TECHSPEC[®] 25.4 x 25.4mm x -50mm FL, Uncoated Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#34-760** **5 In Stock**

-

1

+

S\$155⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$155.00 each
Qty 6-25	S\$139.00 each
Qty 26-49	S\$133.00 each
Need More?	Request Quote

Product Downloads

General	
Cylinder Lens, Plano-Concave	Type:
Physical & Mechanical Properties	
Protective as needed	Bevel:
4.00	Center Thickness CT (mm):

±0.1	Center Thickness Tolerance (mm):
22.86 x 22.86	Clear Aperture CA (mm):
+0.0/-0.025	Dimensional Tolerance (mm):
25.4 x 25.4	Dimensions (mm):
7.22	Edge Thickness ET (mm):
<3	Axial Twist (arcmin):

Optical Properties	
-50.00	Effective Focal Length EFL (mm):
N-BK7	Substrate:
2	f/#:
0.25	Numerical Aperture NA:
Uncoated	Coating:
350 - 2200	Wavelength Range (nm):
-52.64	Back Focal Length BFL (mm):
25.84	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
<5	Plano Axis Wedge (arcmin):
<5	Power Axis Wedge (arcmin):

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Beam Shaping Grade Specifications
- Used with [TECHSPEC® Imaging Grade PCX Cylinder Lenses](#) for Circularizing Beams
- Negative Focal Length

TECHSPEC® Imaging Grade PCV Cylinder Lenses are typically used to diverge collimated light in a single axis. These lenses are designed for system integration due to the tightly controlled specifications and generous volume discounts. TECHSPEC Imaging Grade PCV Cylinder Lenses feature tightly controlled wedge and tilt specifications and are ideal for circularizing elliptical beams in combination with our [TECHSPEC Imaging Grade PCX Cylinder Lenses](#).

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).