


25.4mm Dia., 2 Arcsec, Low Profile Enhanced Aluminum Replicated Hollow Metal Retroreflector



Replicated Hollow Metal Retroreflectors

Stock **#70-637** **1 In Stock**

-

1

+

S\$1,060^{.39}

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,060.39 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Retroreflector

Type:

Low Profile

Style:


Physical & Mechanical Properties	
22.86	Clear Aperture CA (mm):
25.40	Diameter (mm):
20.32	Height (mm):
+0.025/-0.051	Dimensional Tolerance (mm):
Optical Properties	
2	Beam Deviation (arcsec):
Enhanced Aluminum	Coating:
Aluminum	Substrate:
60-40	Surface Quality:
Left-Handed	Image Orientation:
R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Coating Specification:
180	Ray Deviation (°):
250 - 700	Wavelength Range (nm):
Threading & Mounting	
M2 x0.4	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:


PRODUCT DETAILS

- Monolithic Aluminum Construction
- Return Beam Accuracy Unaffected by Vibration
- Bare Gold Coated for High Reflectivity in the Infrared
- Low Profile Versions are Available

Replicated Hollow Metal Retroreflectors feature a monolithic aluminum construction and an integrated mount to provide return beam performance unaffected by vibration. These retroreflectors are coated on their first surface with bare gold, maximizing their reflectivity in the infrared (IR). Designed to have the entirety of their optical path in air, these retroreflectors do not require antireflection coatings for optimal performance and can be used over wider wavelength ranges than glass retroreflectors. Replicated Hollow Metal Retroreflectors are ideal for applications where an optical path through a glass prism is undesired, reduced weight is required, or where high shock and vibration levels are expected. The replication manufacturing process of these optics enables cost-effective designs while providing high performance beam return accuracy.

TECHNICAL INFORMATION





REPLICATED HOLLOW METAL RETROREFLECTORS					
Diameter (mm)	Height (mm)	Mounting Threads	Coating	Stock No.	
				5 Arcseconds	10 Arcseconds
12.7	21.68	10-24	Bare Gold	#15-897	#15-898
19.1	26.17	10-24	Bare Gold	#15-899	#15-900
25.4	30.66	10-24	Bare Gold	#15-901	#15-902
38.1	39.64	10-24	Bare Gold	#15-903	#15-904

