

TECHSPEC[®] 25.4mm Dia., 266nm T, 532 & 1064nm R 45° Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock **#11-548** 1 In Stock

-

1

+

S\$533⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$533.40 each
Qty 6-24	S\$480.20 each
Qty 25-49	S\$427.00 each
Need More?	Request Quote

Product Downloads

General	
Harmonic Beamsplitter	Type:
Physical & Mechanical Properties	
>90	Clear Aperture (%):
Dichroic	Construction:

25.40 +0.00/-0.10	Diameter (mm):
<3	Parallelism (arcmin):
6.35 ±0.20	Thickness (mm):
Optical Properties	
45	Angle of Incidence (°):
Surface 1: R _{abs} : >99% @ 532nm, R _{abs} : >99% @ 1064nm, T _{abs} : >70% @ 266nm Surface 2: R _{abs} : <1.0% @ 266nm	Coating Specification:
532, 1064	Reflection Wavelength (nm):
Fused Silica (Corning 7980)	Substrate: ☐
λ/10	Surface Flatness (P-V):
10-5	Surface Quality:
266	Transmission Wavelength (nm):
Surface 1: 1 J/cm ² @ 266nm, 20ns, 20Hz 5 J/cm ² @ 532nm, 20ns, 20Hz 7.5 J/cm ² @ 1064nm, 20ns, 20Hz Surface 2: 1 J/cm ² @ 20ns, 20Hz @ 266nm	Damage Threshold, By Design: ☐
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- λ/10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

Note: The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

Compatible Mounts