

25.4mm Dia. 300 - 2700nm Broadband Polarizer



Broadband Polarizers

Stock **#89-602** 14 In Stock

-

1

+

S\$1,708⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,708.00 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer

Type:

Physical & Mechanical Properties

19.05

Clear Aperture CA (mm):

25.40

Diameter (mm):

2.50 ±0.3

Thickness (mm):

Dimensional Tolerance (mm):	
+0.0/-0.1	
Optical Properties	
Angle of Incidence (°):	
±40	
Extinction Ratio:	
>100:1 @ 300 - 400nm (Typical) >50,000:1 @ 450 - 550nm (Typical) >800:1 @ 700 - 1400nm (Typical) >1000:1 @ 1400 - 2650nm (Typical)	
Substrate: 	
Fused Silica (Corning 7980)	
Wavelength Range (nm):	
300 - 2700	
Polarization Axis Mark (°):	
±2	
Threading & Mounting	
Mount Thickness (mm):	
4.5	
Environmental & Durability Factors	
Operating Temperature (°C):	
-50 to 80	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	

Product Details

The input beam should enter through the front of the optic, which is the engraved side.

- Wide Acceptance Angles
- Broadband Performance from 300 -2700nm
- Compact Designs Ease System Integration

Broadband Polarizers are ideal solutions for broadband applications from the UV to SWIR where wire grid polarizers are not practical. Broadband Polarizers feature acceptance angles of ±40° and are well suited for use with uncollimated light sources. Additionally, these polarizers utilize a proprietary design that allows for consistent transmitted contrast from 300 – 2700nm.

Note: The input beam should enter through the front of the optic, which is the engraved side.

Technical Information

