

[See all 102 Products in Family](#)

TECHSPEC[®] 25.0mm Diameter x 25.0mm FL, 633nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#65-504** 5 In Stock

☐ [Other Coating Options](#)

-

1

+

S\$85⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	S\$85.40 each
Qty 10-25	S\$77.00 each
Qty 26-49	S\$68.25 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.0/-0.025	
Centering (arcmin):	<1
Center Thickness CT (mm):	8.00 ±0.10
Edge Thickness ET (mm):	2.43
Clear Aperture CA (mm):	24
Bevel:	Protective as needed

Optical Properties	
Effective Focal Length EFL (mm):	25.00 @ 587.6nm
Back Focal Length BFL (mm):	20.22
Coating:	Laser V-Coat (633nm)
Coating Specification:	R _{abs} <0.25% @ 633nm
Substrate: □	N-SF5
Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4
Focal Length Tolerance (%):	±1
Radius R ₁ (mm):	16.82
f#:	1.00
Numerical Aperture NA:	0.50
Design Wavelength DWL (nm):	633
Damage Threshold, By Design: □	5 J/cm ² @ 633nm, 10ns

Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 235:	Compliant

Product Details

- <0.25% Reflection at 633nm for HeNe Applications
- BBAR Coating Options Also Available: [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), 633nm, [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® 633nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 633nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

LASER OPTICS

MADE BY EDMUND OPTICS®



Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts