

TECHSPEC®

25.4 x 25.4mm EFL 90° Protected Silver 100Å Off-Axis Parabolic Mirror



Stock **#36-586** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

S\$377.00

ADD TO CART

Qty 1-5
S\$377.00
Qty 6+
S\$339.30
Volume Pricing
Request Quote

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):
25.40

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 25.40
Coating: Protected Silver (450-12000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥98% @ 2,000 - 12,000nm, R _{avg} (typical) 96% @ 450 - 2,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 12.7
Surface Figure, RMS: λ/4
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 450 - 12000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-111
Substrate: Aluminum 6061-T6
Y Offset (mm): 25.4
Reflected Wavefront, RMS: λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant