

[See all 23 Products in Family](#)

TECHSPEC® 25.4 x 76.2mm EFL 90° Protected Silver 100Å Off-Axis Parabolic Mirror



Stock **#36-588** **3 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **S\$600⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	S\$600.60 each
Qty 6-10	S\$539.00 each
Qty 11-25	S\$518.00 each
Need More?	Request Quote

Product Downloads

General

Off-Axis Parabolic Mirror **Type:**

Physical & Mechanical Properties

76.2 **Y Offset (mm):**

25.40 +0.00/-0.38 **Diameter (mm):**

90 Clear Aperture (%):

<100 RMS Surface Roughness (\square):

Optical Properties

Metal Coating Type:

Protected Silver (450-12000nm) Coating:

90 Off-Set Angle ($^{\circ}$):

450 - 12000 Wavelength Range (nm):

76.20 Effective Focal Length EFL (mm):

Aluminum 6061-T6 Substrate: \square

Coating Specification:
 $R_{avg} \geq 98\%$ @ 2,000 - 12,000nm,
 R_{avg} (typical) 96% @ 450 - 2,000nm

± 1 Focal Length Tolerance (%):

38.1 Parent Focal Length PFL (mm):

$\lambda/4$ Surface Figure, RMS:

80-50 Surface Quality:

76.20 Radius of Curvature (mm):

$\lambda/2$ Reflected Wavefront, RMS:

Threading & Mounting

#47-111 Compatible Mounting Plates:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:


Compliant Reach 247:

Product Details

- Protected Silver Coating for Visible and IR Application
- 100A Surface Roughness
- 90° Offset Angle
- Aluminum and Gold Coated Off-Axis Parabolic Mirrors Also Available

TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are designed to direct and focus incident collimated light at a specific offset angle with minimal scatter loss. Coated with protected silver, these OAP mirrors provide high reflectivity from the visible to the infrared (IR), making them ideal for broadband applications. These Silver OAPs provide unobstructed access to the point of focus, allowing for the creation of more compact systems. TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are commonly used in instrumentation and laser systems in the visible and IR spectrum, including Schlieren, MTF, FLIR, and FTIR systems. For additional surface roughness options and offset angles, please see our aluminum or gold coated OAPs or [contact us](#) for custom options.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
