

TECHSPEC® 25.4mm Dia. x 300mm FL, 532nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#38-704** 3-5 DAYS

[Other Coating Options](#)

- 1 + **S\$294.35**

ADD TO CART

Qty 1-5
S\$294.35
Qty 6+
S\$234.90
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.025

Effective Focal Length EFL (mm):
300.00 @ 355nm

Back Focal Length BFL (mm):
297.38

Coating: Laser V-Coat (532nm)
Coating Specification: R_{abs} <0.25% @ 532nm
Substrate: Fused Silica (Corning 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 3.39
Radius R₁ (mm): 142.83
Clear Aperture CA (mm): 21.59
f/#: 11.81
Numerical Aperture NA: 0.04
Design Wavelength DWL (nm): 532
Type: Plano-Convex Lens
Bevel: Protective Bevel As Needed
Damage Threshold, By Design: 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View