

[See all 8 Products in Family](#)

## 25.4mm Dia., 2mm Thick, Uncoated, ISP Optics IR Fused Silica Window | QI-W-25-2

See More by [ISP Optics](#)



Stock #24-585 CLEARANCE **10 In Stock**

⊖ 1 ⊕ **\$\$158<sup>13</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>\$\$158.13</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Protective Window **Type:**

QI-W-25-2 **Model Number:**

#### Physical & Mechanical Properties

Protective as needed **Bevel:**

85 **Clear Aperture (%):**

21.59	Clear Aperture CA (mm):
25.40 +0.00/-0.13	Diameter (mm):
2.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
522.00	Knoop Hardness (kg/mm <sup>2</sup> ):
<3	Parallelism (arcmin):
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):

## Optical Properties

67.8	Abbe Number (v <sub>d</sub> ):
Uncoated	Coating:
1.458	Index of Refraction (n <sub>d</sub> ):
Fused Silica	Substrate:
1λ	Surface Flatness (P-V):
40-20	Surface Quality:
200 - 3500	Wavelength Range (nm):

## Material Properties

0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):
2.20	Density (g/cm <sup>3</sup> ):

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 240:

## Product Details

- Excellent Thermal Stability
- Low Auto-Fluorescence
- IR Grade Fused Silica

ISP Optics Fused Silica Windows feature high transmission across the Ultraviolet (UV), Visible (VIS), and Infrared (IR) spectrum with IR Grade substrates extending up to 3500nm with no absorption bands. Fused Silica is a commonly used material for precision optics due to its consistent and repeatable optical performance. In addition, fused silica features a low coefficient of thermal expansion that provides high thermal stability and resistance to thermal shock. ISP Optics Fused Silica Windows provide extremely low fluorescence, making them ideal for a wide range of UV and IR laser applications.