


[See all 4 Products in Family](#)

25.4mm Dia. x 150mm FL, 3-5µm BBAR Coated, ISP Optics Silicon (Si) PCX Lens | HDAR35-SI-PX-25-150

See More by [ISP Optics](#)



Stock #24-895 CLEARANCE 2 In Stock

⊖ 1 ⊕ S\$344⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | S\$344.40 each |
| Need More? | Request Quote |

Product Downloads

General

Plano-Convex Lens Type:
 HDAR35-SI-PX-25-150 Model Number:

Physical & Mechanical Properties

25.40 +0.00/-0.13 Diameter (mm):

| | |
|----------------------|----------------------------------|
| <3 | Centering (arcmin): |
| 2.20 ±0.20 | Center Thickness CT (mm): |
| 2.00 | Edge Thickness ET (mm): |
| 22.86 | Clear Aperture CA (mm): |
| Protective as needed | Bevel: |

Optical Properties

| | |
|---|--|
| 150.00 @4μm | Effective Focal Length EFL (mm): |
| BBAR (3000-5000nm) | Coating: |
| R _{avg} <0.5% @3 - 5μm R _{abs} <1.5% @3 - 5μm | Coating Specification: |
| Silicon (Si) | Substrate: <input type="checkbox"/> |
| 80-50 | Surface Quality: |
| 1λ | Irregularity (P-V) @ 632.8nm: |
| ±2 | Focal Length Tolerance (%): |
| 363.54 | Radius R₁ (mm): |
| 5.91 | f/#: |
| 0.08 | Numerical Aperture NA: |
| 3000 - 5000 | Wavelength Range (nm): |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 240: |

Product Details

- High-Durability Anti-Reflection (HDAR) Coated for 3 - 5μm
- Ideal for Weight Sensitive Applications
- Available Focal Lengths from 25.4 – 500mm

ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses feature a High Durability Anti-Reflection (HDAR) coating for increased transmission in the 3 - 5μm range. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. In addition, the HDAR coating increases the durability of the substrate, enabling use in harsh environments. ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses also feature a low density of 2.329g/cm³, making them ideal for weight-sensitive IR applications such as Near-Infrared (NIR) imaging and infrared spectroscopy.