

[See all 4 Products in Family](#)

25.4mm Dia. x 25.4mm FL, Uncoated, ISP Optics Silicon (Si) Aspheric Lens | ASPH-SI-25-25

See More by [ISP Optics](#)



Stock **#24-882** CLEARANCE **3 In Stock**

-

1

+

S\$501²⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$501.20 each
Need More?	Request Quote

Product Downloads

General	
ASPH-SI-25-25	Model Number:
Physical & Mechanical Properties	
25.40 +0.00/-0.13	Diameter (mm):
<20	Centering, ETD (μm):
22.86	Clear Aperture CA (mm):

1.73	Edge Thickness ET (mm):
3.00 ±0.20	Center Thickness CT (mm):
Protective as needed	Bevel:
Concave	Shape of Back Surface:
<100 Ra	Surface Roughness (□):

Optical Properties	
25.40	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
23.15	Back Focal Length BFL (mm):
Silicon (Si)	Substrate: □
Uncoated	Coating:
60-40	Surface Quality:
1.00	f/#:
1200 - 7000	Wavelength Range (nm):
Infinite	Conjugate Distance:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Transmission from 1.2 - 7µm
- Diffraction-Limited Performance
- Available Uncoated or HDAR Coated for 3 - 5µm

ISP Optics Silicon (Si) Aspheric Lenses provide diffraction-limited performance for weight-sensitive, Mid-Wave Infrared (MMR) applications. Available uncoated for applications in the 1.2 - 7µm range or with a high durability anti-reflection (HDAR) coating in the 3 - 5µm range, these lenses are ideal for harsh environment or black body radiation applications. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. ISP Optics Silicon (Si) Aspheric Lenses feature a low density of 2.329g/cm³, making them lightweight alternatives to Germanium and Zinc Selenide.