

25.4mm Travel, Metric Micrometer, Solid Top 66.5mm Stage



Stock **#55-462** 5 In Stock

-

1

+

S\$2,121^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$2,121.00 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Solid Top	Note:
Physical & Mechanical Properties	
Linear (X)	Type of Movement:
Ball Bearing	Guide System:
	Drive Orientation:

Center Drive	
66.5 x 66.5	Stage Size (mm):
25	Travel (mm):
Aluminum Top and Base/440C Stainless Steel Bearings	Construction:
0.001	Graduation (mm):
28	Load Capacity, Normal (kg):
4.5	Load Capacity, T _a (kg):
0.9	Load Capacity, T _b (kg):
2.62 x 2.62	Stage Size (inches):
2 per 25 mm of travel	Straight Line Accuracy (µm):
630	Weight (g):

Hardware & Interface Connectivity

Digital Micrometer (Metric)	Type of Drive:
-----------------------------	----------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:


Product Details

- 0.001mm Resolution Directly Readable Micrometer
 - Readout in Inches or Millimeters
 - Available with English or Metric Mounting Holes
- Available with standard (English) or metric mounting holes, these digital micrometers have a precision ground mounting surface and clear LCD readout. The micrometers also feature incremental or absolute positional modes, zero set at any position, inch or millimeter readouts (0.001mm resolution), display hold, and automatic shutdown to conserve the integral battery. Stage travels are one inch and table tops are available with or without a thru-hole.


Technical Information

Figure	Size A	Size B	Size C	Size D	Size E	Size F	Threading G	Threading H	Stock No.
Solid Top									
A	1.75"	0.75"	1.12"	2.12"	1.00"	0.50"	6-32	#6	#53-857
A	1.75"	0.75"	1.12"	2.12"	1.00"	—	6-32	#6	#53-856
A	2.62"	1.00"	2.00"	3.00"	2.00"	—	10-32	#¼	#38-199
A	2.62"	1.00"	2.00"	3.00"	2.00"	1.00"	10-32	#¼	#38-203
B	5.00"	1.00"	4.00"	—	4.00"	—	¼-20	#¼	#38-202
B	5.00"	1.00"	4.00"	—	4.00"	2.00"	¼-20	#¼	#38-204
C	44.4mm	19.0mm	30.0mm	53.8mm	25.0mm	—	M4	M4	#55-461
C	66.5mm	25.4mm	50.0mm	75.9mm	50.0mm	—	M5	M6	#55-462
D	127.0mm	25.4mm	100.0mm	—	—	—	M6	M6	#55-463
D	66.5mm	25.4mm	50.0mm	75.9mm	50.0mm	25.4mm	M5	M6	#55-464


Digital Micrometer Positioning Stage (Figure A)



Digital Micrometer Positioning Stage (Figure B)



Digital Micrometer Positioning Stage (Figure C)



Digital Micrometer Positioning Stage (Figure D)

