

TECHSPEC[®] 25.4 x 6.35mm, 10' Wedge, Mirror Substrate



TECHSPEC[®] Laser Mirror Substrates

Stock **#21-252** 16 In Stock

-

1

+

S\$161⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$161.00 each
Qty 11-25	S\$144.20 each
Qty 26-50	S\$128.10 each
Need More?	Request Quote

Product Downloads

General	
Laser Mrror Substrate	Type:
Physical & Mechanical Properties	
10 ±5	Parallelism (arcmin):
80	Clear Aperture (%):

Commercial Polish	Back Surface:
25.40 +0.00/-0.10	Diameter (mm):
6.35 ±0.01	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
λ/10	Surface Flatness (P-V):
Uncoated	Coating:
Fused Silica (Corning 7980)	Substrate: ☐
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- λ/10 and λ/20 Surface Flatness and 10-5 Surface Quality
- High Quality Fused Silica Substrates
- Imperial Sizes with Circular or Rectangular Geometries
- Window Substrates Also Available

TECHSPEC® Laser Mirror Substrates are manufactured from high quality fused silica and are designed for use with high power laser sources. These mirrors feature excellent surface specifications, including λ/10 and λ/20 surface flatness and 10-5 surface quality, to limit the possibility of reduced performance due to surface defects. The high surface quality of these mirror blanks also makes them ideal for use in demanding intra-cavity laser applications. TECHSPEC Laser Mirror Substrates are available in standard imperial sizes, with either circular or rectangular geometries. Please contact us if your application requires a custom size laser mirror substrate.

Compatible Mounts