

## 25mm 2 MegaPixel Fixed Focal Length Lens



25mm Fixed Focal Length, #14-399

Stock #14-399 **3 In Stock**

S\$568<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	S\$568.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Fixed Focal Length Lens **Type:**

### Physical & Mechanical Properties

Variable **Iris Option:**

33.39 **Length (mm):**

32.5 **Maximum Diameter (mm):**

Weight (g):

60

## Optical Properties

Horizontal Field of View @ Max Sensor Format:  
19.42°

Horizontal Field of View, 2/3" Sensor:  
19.42°

Horizontal Field of View, 1/2" Sensor:  
14.59°

Horizontal Field of View, 1/3" Sensor:  
10.97°

Horizontal Field of View, 1/4" Sensor:  
7.32°

Maximum Image Circle (mm):  
11.00

Focal Length FL (mm):  
25.00

Working Distance (mm):  
300 - ∞

Aperture (f/#):  
f/1.4 - f/32

Distortion (%):  
<-1

Lens Wavelength Range:  
VS

## Sensor

Maximum Sensor Format:  
2/3"

## Threading & Mounting

Filter Thread:  
M30.5 x 0.50 (Female)

Mount:  
C-Mount

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

- 2 MegaPixel Resolution Design
- Lockable, Manual Focus and Iris
- Fixed Focal Lengths from 4 to 50mm
- C-Mount Lens Mount

2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover 1/2" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.