

[See all 130 Products in Family](#)

TECHSPEC® 25mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #47-981 [CONTACT US](#)

1 **\$243⁰⁰**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | \$243.60 each |
| Qty 6-25 | \$214.20 each |
| Need More? | Request Quote |

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

Clear Aperture (%):

| | |
|---|--|
| >90 | |
| Ground | Back Surface: |
| 25.00 +0.00/-0.20 | Diameter (mm): |
| 6.00 ±0.20 | Thickness (mm): |
| Optical Properties | |
| 10-5 | Surface Quality: |
| 99.5 | Reflection at DWL (%): |
| Coating Specification: R _{abs} >99.5% @ 266nm @ 45° AOI R _{avg} >99.5% @ 263 - 268nm @ 45° AOI | |
| 263 - 268 | Wavelength Range (nm): |
| λ/10 | Surface Flatness (P-V): |
| Dielectric | Coating Type: |
| Laser Mirror (266nm) | Coating: |
| 266 | Design Wavelength DWL (nm): |
| 45 | Angle of Incidence (°): |
| Fused Silica (Corning 7980) | Substrate: <input type="checkbox"/> |
| Damage Threshold, Reference: <input type="checkbox"/> 2.5 J/cm ² @ 266nm, 20ns, 20Hz | |

| | |
|------------------------------|------------------------------------|
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| Compliant | Reach 209: |
| View | Certificate of Conformance: |

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts