

TECHSPEC® 25mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror



Nd:YAG ZERODUR Laser Line Mirrors

Stock **#26-417** 5 In Stock

-

1

+

S\$322⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$322.00 each
Qty 6-25	S\$291.20 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Laser Mirror

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.00/-0.20	
>90	Clear Aperture (%):
30	Parallelism (arcsec):
4.00 +/-0.2	Thickness (mm):
Optical Properties	
355	Design Wavelength DWL (nm):
351 - 358	Wavelength Range (nm):
ZERODUR®	Substrate:
45	Angle of Incidence (°):
99.8	Reflection at DWL (%):
Laser Mirror (355nm)	Coating:
Coating Specification: R _{abs} >99.8% @ 355nm @ 45° AOI R _{avg} >99.5% @ 351 - 358nm @ 45° AOI	
Dielectric	Coating Type:
λ/10	Surface Flatness (P-V):
20-10	Surface Quality:
Damage Threshold, By Design: 6 J/cm ² @ 355nm, 20ns, 20Hz	
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.5% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Nd:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Nd:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of ±0.10 x 10-6/°C these mirrors are ideal for applications where the optics will be exposed to fluctuating temperatures. The Nd:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Nd:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with λ/10 flatness and 20-10 surface quality. These mirror are an excellent fit for laboratories and integration into larger powerful laser systems