


25mm Dia. High Contrast UV Polarizer



Stock **#36-651** 1 In Stock

-

1

+

S\$1,106^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	S\$1,106.00 each
Qty 10+	S\$1,050.00 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):

22.50

Diameter (mm):

25.00

Thickness (mm):

2.00 ±0.2

+0.0/-0.2	Dimensional Tolerance (mm):
Nanoparticle	Construction:
90	Clear Aperture (%):

Optical Properties	
±20	Angle of Incidence (°):
>100,000:1 (372nm - 388nm) >10,000:1 (369nm - 390nm) >1,000:1 (365nm - 395nm)	Extinction Ratio:
Soda Lime Float Glass	Substrate: ☐
>51	Transmission (%):
< λ/4	Transmitted Wavefront, P-V:
<1	Beam Deviation (arcmin):
±2	Polarization Axis Mark (%):
365 - 395	Wavelength Range (nm):

Environmental & Durability Factors	
-20 to +80	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25µm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

Technical Information

