



TECHSPEC®

25mm Dia., VIS Broadband Dielectric, $\lambda/10$ Stemmed Mirror



Stock #16-734 CLEARANCE 3-5 DAYS

-

1

+

S\$229.10

ADD TO CART

Qty 1-5

S\$229.10

Qty 6+

S\$183.42

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):
 $\lambda/10$

Substrate: Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R_{avg} ≥98% @400 - 750nm (0 - 45°, All Polarizations) R_{avg} ≥99% @400 - 750nm (0 - 45°, S-Polarization)
Coating: Dielectric Mirror (400-750nm)
Coating Type: Dielectric
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 400 - 750
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20
Damage Threshold, Reference: 0.5J/cm², 20ns, 20Hz @532nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View