

TECHSPEC® 25mm Dia x 15mm FL 8-12μm Coated, Ge Aspheric Lens



Stock **#68-252** 3-5 DAYS

[Other Coating Options](#)

- 1 + **S\$1,558.75**

ADD TO CART

Qty 1-5
S\$1,558.75
Qty 6+
S\$1,247.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
15.00 @ 4000nm

Numerical Aperture NA:
0.83

Back Focal Length BFL (mm):

14.00
Substrate: Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <3.0% @ 8 - 12μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.47
Center Thickness CT (mm): 4.00 ±0.10
f/#: 0.6
Bevel: Protective bevel as needed
Edges: Diamond Turned
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant