


TECHSPEC® 25mm Dia x 25mm FL BBAR (1650-3000nm) Coated, Si Aspheric Lens



Stock #24-289 **5 In Stock**

- 1 + \$994.00

ADD TO CART

Volume Pricing	
Qty 1-5	\$994.00 each
Qty 6+	\$798.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

25.00 +0.00/-0.10 **Diameter (mm):**

≤10 **Centering (arcmin):**

Centering, ETD (μm):

<21.8	Clear Aperture CA (mm):
22.5	
	Edge Thickness ET (mm):
2.44	
	Center Thickness CT (mm):
3.80 ±0.10	
	Bevel:
Protective as needed	
	Edges:
Diamond Turned	
	Shape of Back Surface:
Concave	

Optical Properties

	Effective Focal Length EFL (mm):
25.00 @4000nm	
	Numerical Aperture NA:
0.50	
	Back Focal Length BFL (mm):
22.50	
	Substrate: <input type="checkbox"/>
Silicon (Si)	
	Asphere Figure Error, RMS @ 632.8nm:
λ/6	
	Coating:
BBAR (1650-3000nm)	
	Coating Specification:
R _{avg} <1% @ 1650 - 3000nm	
R _{abs} <2% @ 1650 - 3000nm	
	Surface Accuracy, P-V (μm):
<0.3	
	Surface Quality:
60-40	
	f#:
1.00	
	Radius R₂ (mm):
43.582	
	Wavelength Range (nm):
1650 - 3000	
	Conjugate Distance:
Infinite	

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- Diffraction-Limited Performance
- Low Density and Dispersion
- Ideal for Weight Sensitive IR Applications
- Available with BBAR (1650-3000nm) or Mid-Wave Infrared (3000-5000nm) AR Coatings

TECHSPEC® Silicon Aspheric Lenses are high performance, lightweight solutions for BBAR and Mid-Wave Infrared (MMIR) applications and are ideal alternatives for costly ZnSe lenses and brittle Germanium lenses. These lenses are available with efficient broadband AR coatings for the BBAR (1650-3000nm) or MMIR (3000-5000nm) spectral regions. TECHSPEC Silicon Aspheric Lenses feature the mechanical and thermal properties required to withstand many of the effects of harsh environments including fluctuations in temperature and pressure. Because silicon is a low density material, these lenses are also ideal for weight-sensitive systems, such as those found in many defense applications.