See all 245 Products in Family

# TECHSPEC® 25mm Dia. x 300mm FL, UV-AR Coated, UV Double-Convex Lens

UV Fused Silica Double-Convex (DCX) Lenses

Stock **#48-313** **14 In Stock**

Other Coating Options

- 1 + S$222.60

ADD TO CART

| Volume Pricing | |
|---|---|
| Qty 1-5 | **S$222.60** each |
| Qty 6-25 | **S$177.80** each |
| Qty 26-49 | **S$166.60** each |
| Need More? | Request Quote |

Product Downloads

## General

**Type:**

Double-Convex Lens

## Physical & Mechanical Properties

**Diameter (mm):**

25.00 +0.0/-0.025

**Centering (arcmin):**

<1

**Bevel:**

Protective as needed

**Center Thickness CT (mm):**

3.09 ±0.10

**Edge Thickness ET (mm):**

2.52

**Clear Aperture CA (mm):**

24.00

## Optical Properties

**Back Focal Length BFL (mm):**

298.94

**Effective Focal Length EFL (mm):**

300.00

**Coating:**

UV-AR (250-425nm)

**Coating Specification:**

$R_{abs}$ ≤1.0% @ 250 - 425nm
$R_{avg}$ ≤0.75% @ 250 - 425nm
$R_{avg}$ ≤0.5% @ 370 - 420nm

**Substrate:**

**Fused Silica** (Corning 7980)

**Surface Quality:**

40-20

**Power (P-V) @ 632.8nm:**

1.5λ

**Irregularity (P-V) @ 632.8nm:**

λ/4

**Radius $R_1$=-$R_2$ (mm):**

274.60

**f/#:**

12.00

**Focal Length Specification Wavelength (nm):**

587.6

**Focal Length Tolerance (%):**

±1

**Numerical Aperture NA:**

0.04

**Wavelength Range (nm):**

250 - 425

**Damage Threshold, Reference:**

3 J/cm$^2$ @ 355nm, 10ns

## Regulatory Compliance

**RoHS 2015:**

**Compliant**

**Certificate of Conformance:**

**View**

**Reach 235:**

**Compliant**

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our **custom manufacturing capabilities** or submit an inquiry **here.**

# Product Details

- Ideal for Imaging Applications
- Mnimize Aberrations Including Spherical and Coma
- Precision Fused Silica Substrate

TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses, also referred to as bi-convex lenses, have two positive, symmetrical faces with equal radii on both sides. These lenses are generally recommended for finite imaging applications with a conjugate ratio (ratio between object distance and image distance) between 0.2 and 5. At a conjugate ratio of 1, aberrations such as spherical aberration, chromatic aberration, coma, and distortion are minimized or canceled due to the symmetric lens design. TECHSPEC® UV Fused Silica Double-Convex (DCX) Lenses have a precision fused silica substrate. These lenses are available uncoated or with UV-AR, UV-VIS, VIS-EXT, VIS-NIR, VIS 0°, NIR I, or NIR II coatings.

# Technical Information







*UV FS Transmission Curve*

| FUSED SILICA | |
|---|---|
|  | Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.<br>**Click Here to Download Data** |
|  | Typical transmission of a 3mm thick fused silica window with MgF2 (400-700nm) coating at 0° AOI.<br>The blue shaded region indicates the coating design wavelengh range, with the following specification:<br>$R_{avg} \leq 1.75\%$ @ 400 - 700nm (N-BK7)<br>Data outside this range is not guaranteed and is for reference only.<br>**Click Here to Download Data** |
|  | Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.<br>The blue shaded region indicates the coating design wavelengh range, with the following specification:<br>$R_{abs} \leq 1.0\%$ @ 250 - 425nm<br>$R_{avg} \leq 0.75\%$ @ 250 - 425nm<br>$R_{avg} \leq 0.5\%$ @ 370 - 420nm<br>Data outside this range is not guaranteed and is for reference only.<br>**Click Here to Download Data** |




Click Here to Download Data




Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{abs} \leq 1.0\%$ @ 350 - 450nm
$R_{avg} \leq 1.5\%$ @ 250 - 700nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{avg} \leq 0.5\%$ @ 350 - 700nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{abs} \leq 0.25\%$ @ 880nm
$R_{avg} \leq 1.25\%$ @ 400 - 870nm
$R_{avg} \leq 1.25\%$ @ 890 - 1000nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{avg} \leq 0.4\%$ @ 425 - 675nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{abs} \leq 0.25\%$ @ 532nm
$R_{abs} \leq 0.25\%$ @ 1064nm
$R_{avg} \leq 1.0\%$ @ 500 - 1100nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{avg} \leq 0.5\%$ @ 600 - 1050nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data




Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelengh range, with the following specification:

$R_{abs} \leq 1.5\%$ @ 750 - 800nm
$R_{abs} \leq 1.0\%$ @ 800 - 1550nm
$R_{avg} \leq 0.7\%$ @ 750 - 1550nm

Data outside this range is not guaranteed and is for reference only.

Click Here to Download Data

## Compatible Mounts

;