

TECHSPEC[®] 25mm Dia. x 50mm FL, 532nm V-Coat, Hyperbolic Aspheric Lens



Hyperbolic Aspheric Lenses

Stock **#89-432** **20+ In Stock**

☐ [Other Coating Options](#)

-

1

+

S\$373³⁸

ADD TO CART

Volume Pricing	
Qty 1-5	S\$373.38 each
Qty 6-25	S\$325.58 each
Qty 26-49	S\$294.22 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Aspheric Lens

Type:

Physical & Mechanical Properties	
25.00 +0.0/-0.1	Diameter (mm):
≤5	Centering (arcmin):
23.00	Clear Aperture CA (mm):
1.49	Edge Thickness ET (mm):
4.30 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:
Convex	Shape of Back Surface:
Optical Properties	
50.00 @ 532nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
50.00	Back Focal Length BFL (mm):
N-BK7	Substrate: ☐
532	Aspheric Design Wavelength (nm):
Laser V-Coat (532nm)	Coating:
R _{abs} <0.25% @ 532nm	Coating Specification:
40-20	Surface Quality:
2.00	f/#:
25.97	Radius R ₂ (mm):
Infinite	Conjugate Distance:
1.6λ RMS and 6λ PV	Asphere Figure Error, @ 632.8nm:
20.00	Power (diopters):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:


PRODUCT DETAILS

Unlike traditional focusing lenses, these lenses should be used with the plano side facing the light source.


- Designed and Coated for Nd:YAG Laser Wavelengths
- Aspheric Figure Error of 1.6λ RMS and 6λ PV
- Modified [TECHSPEC® PCX Lenses](#)

TECHSPEC® Hyperbolic Aspheric Lenses are [TECHSPEC® PCX Lenses](#) that have been modified to include a mild aspheric surface to provide superior performance at specified wavelengths. Unlike the preexisting spherical lenses, TECHSPEC Hyperbolic Aspheric Lenses produce diffraction-limited spot sizes at the design wavelength, which is ideal for focusing or collimating applications. Any standard lens from Edmund Optics can be modified similarly to TECHSPEC Hyperbolic Aspheric Lenses to create your ideal surface and offer a low-cost boost to performance and to provide the best solution for specific application needs.

Note: Unlike traditional focusing lenses, these lenses should be used with the plano side facing the light source.



TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS