

25mm Dia. x 400mm FL Uncoated, DCX N-K5 Lens



Stock #32-904 CLEARANCE 20+ In Stock

-

1

+

S\$33^{.25}

ADD TO CART

Volume Pricing	
Qty 1+	S\$33.25 each
Need More?	Request Quote

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.00/-0.10

Centering (arcmin):

<1

Center Thickness CT (mm):

5.00 ±0.10


Edge Thickness ET (mm):

4.63	
24	Clear Aperture CA (mm):
	Bevel:
Protective as needed	
Optical Properties	
400.00 @ 587.6nm	Effective Focal Length EFL (mm):
398.75	Back Focal Length BFL (mm):
Uncoated	Coating:
N-K5	Substrate: ☐
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
16.00	f#:
0.03	Numerical Aperture NA:
330 - 2500	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- N-K5 Substrate
 - Various Anti-Reflection (AR) Coatings
 - PCX and DCX Options Available
- N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

Technical Information



Compatible Mounts