

TECHSPEC[®] 25mm Dia. x 50mm FL, YAG-BBAR Coated, Achromatic Lens



YAG-BBAR Coated Achromatic Lenses



Stock #33-209 13 In Stock

[Other Coating Options](#)

-

1

+

S\$179²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$179.20 each
Qty 6-25	S\$142.80 each
Qty 26-49	S\$133.70 each
Need More?	Request Quote

Product Downloads

General

Type:

Achromatic Lens

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.000/-0.025	
24.00	Clear Aperture CA (mm):
<1	Centering (arcmin):
11.50 ±0.20	Center Thickness CT (mm):
9.00 ±0.10	Center Thickness CT 1 (mm):
2.5 ±0.10	Center Thickness CT 2 (mm):
8.79	Edge Thickness ET (mm):
Protective as needed	Bevel:

Optical Properties	
50.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
43.53	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
34.53	Radius R ₁ (mm):
21.98	Radius R ₂ (mm):
214.63	Radius R ₃ (mm):
N-BAF10 / N-SF10	Substrate: □
40-20	Surface Quality:
2.00	f/#:
0.25	Numerical Aperture NA:
YAG-BBAR (500-1100nm)	Coating:
R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
500 - 1100	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

Product Details

- Optimized for <0.25% Absolute Reflectivity at 532nm and 1064nm
- Excellent Broadband Transmission from 500 - 1100nm
- Low Cost Alternative to Air-Spaced Focusing Doublets

TECHSPEC® YAG-BBAR Coated Achromatic Lenses consist of two optical components cemented together to form a doublet that is ideal for correcting on-axis spherical and chromatic aberrations. These achromats feature a broadband anti-reflective coating with superior transmission from 500 - 1100nm, and are optimized for less than 0.25% absolute reflectivity at 532 and 1064nm. Our TECHSPEC® YAG-BBAR Coated Achromatic Lenses are specifically designed to minimize the spot size for polychromatic illumination within the recommended usable wavelength range, but may also be used for focusing Nd:YAG lasers, especially those with an alignment beam.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

;