

TECHSPEC[®] 25mm Dia. x 50mm FL 785nm V-Coat, UV PCX Lens



Stock #25-914 4 In Stock

-

1

+

S\$253^{.40}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$253.40 each
Qty 6-25	S\$203.00 each
Qty 26-49	S\$190.40 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

25.00 +0.0/-0.025

Diameter (mm):

Protective as needed

Bevel:

5.84	Center Thickness CT (mm):
<1	Centering (arcmin):
24	Clear Aperture CA (mm):
2.13	Edge Thickness ET (mm):

Optical Properties

50.00 @ 587.6nm	Effective Focal Length EFL (mm):
Fused Silica	Substrate:
2	f#:
0.25	Numerical Aperture NA:
785nm V-Coat	Coating:
46.00	Back Focal Length BFL (mm):
R _{abs} <0.25% @ 785nm	Coating Specification:
785	Design Wavelength DWL (nm):
±1	Focal Length Tolerance (%):
22.92	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- <0.25% Reflection at 785nm
 - 5 - 50mm Diameters Available
 - 10 - 250mm EFL Designs Available
 - 405nm, 532nm, 1064nm, and 1550nm V-Coated Options Offered
- TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.