

TECHSPEC[®] 25mm Dia x -100mm FL MgF₂ Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#48-382** **1 In Stock**

-

1

+

S\$123⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	S\$123.00 each
Qty 6-25	S\$110.00 each
Qty 26-49	S\$104.00 each
Need More?	Request Quote

Product Downloads

General	
Cylinder Lens, Plano-Concave	Type:
Physical & Mechanical Properties	
25.00 +0.0/-0.2	Diameter (mm):
3.50	Center Thickness CT (mm):


±0.1	Center Thickness Tolerance (mm):
5.03	Edge Thickness ET (mm):
Optical Properties	
-100.00	Effective Focal Length EFL (mm):
N-BK7	Substrate: ☐
4.00	f/#:
0.13	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
400 - 700	Wavelength Range (nm):
-102.31	Back Focal Length BFL (mm):
R _{avg} ≤1.75% @ 400 - 700nm	Coating Specification:
±3	Focal Length Tolerance (%):
-51.68	Radius R ₁ (mm):
60-40	Surface Quality:
10 J/cm ² @ 532nm, 10ns	Damage Threshold, By Design: ☐

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence
 - Circular and Rectangular Form Factors
 - Multiple Coating Options Available
- TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.
- The thin lens approximation for the length of a line generated by a negative cylinder lens is: $L = 2 * (r_0/f) * (z + f)$ where L is the line length, r_0 is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

Technical Information



Coating Curves

Custom

- Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.
- Our capabilities include:
- Custom dimensions, materials, coatings, and more

- High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

;