

TECHSPEC[®] 25mm Minor Axis Uncoated, Fused Silica Brewster Window



Stock **#65-827** 9 In Stock

-

1

+

S\$200^{.20}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$200.20 each
Qty 11+	S\$179.20 each
Need More?	Request Quote

Product Downloads

General

Type:
Linear Polarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):
22.50 x 39.79

Thickness (mm):
2.00 ±0.20

Edges:
Fine Ground

44.21	Major Axis (mm):
25.00 +0.00/-0.25	Minor Axis (mm):
≤10	Parallelism (arcsec):
73	Young's Modulus (GPa):
Brewster Window	Construction:

Optical Properties	
Uncoated	Coating:
632.8	Design Wavelength DWL (nm):
1.458	Index of Refraction (n _d):
Fused Silica (Corning 7980)	Substrate: ☐
10-5	Surface Quality:
λ/10	Transmitted Wavefront, P-V:
200 - 2200	Wavelength Range (nm):

Material Properties	
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Reduce Loss of P-Polarized Light
- Circular Profile When Oriented at 55.57°
- Great for Use in Laser Cavities

TECHSPEC® Brewster Windows are designed to present a circular profile when oriented at Brewster’s angle (55.57°). TECHSPEC® Brewster Windows feature laser grade surface quality and parallelism, in addition to limiting transmitted wavefront distortion to λ/10. When used at 55.57°, these windows minimize the loss of P-polarized light, ideal for use within laser cavities and for producing linearly polarized light.


LASER OPTICS

MADE BY EDMUND OPTICS®



[LEARN MORE](#)

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

