

## 25mm FL SWIR Series Fixed Focal Length Lens



Stock #68-688 **1 In Stock**

[Similar Products](#)

⊖ 1 ⊕ S\$3,201<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	S\$3,201.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Product Family:**  
1" SWIR Series Fixed Focal Length Lenses

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**  
43.00

43 Maximum Diameter (mm):

43 Outer Diameter (mm):

135 Weight (g):

### Optical Properties

150.00 Field of View @ Min Working Distance (mm):

29.3° Horizontal Field of View, 1" Sensor:

16.00 Maximum Image Circle (mm):

25.00 Focal Length FL (mm):

300 - ∞ Working Distance (mm):

f/1.4 - f/16 Aperture (f/#):

<-1.0 Distortion (%):

-1 Maximum Distortion (%):

SWR Lens Wavelength Range:

### Sensor

1" Maximum Sensor Format:

4.50 Pixel Size (µm):

### Threading & Mounting

M35.5 x 0.5 Filter Thread:

C-Mount Mount:

### Regulatory Compliance

[Exempt](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Contains SVHC\(s\)](#) REACH 241:

## Product Details

- 1", C-Mount Lens
- Spectral Range of 800 - 2000nm for InGaAs SWIR Sensors
- 8mm to 50mm Focal Lengths

Short Wave Fixed Focal Length Lenses are the best choice for use with SWIR cameras. The SWIR spectrum is an ideal choice for a variety of applications, including solar cell inspection, security, and biomedical imaging. When utilized in conjunction with a SWIR camera, these lenses will permit imaging through silicon, imaging outdoors without additional illumination, detecting bruising on fruit, and a host of additional infrared applications.

## Technical Information



