

[See all 30 Products in Family](#)

**TECHSPEC® 25mm, Uncoated, High Tolerance N-BK7 Right Angle Prism**



N-BK7 High Tolerance Right Angle Prisms

Stock #32-549 [CONTACT US](#)

⊖ 1 ⊕ **S\$163<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>S\$163.80</b> each
Qty 6-25	<b>S\$130.90</b> each
Qty 26-49	<b>S\$123.20</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Right Angle Prism **Type:**

**Physical & Mechanical Properties**

+0/-0.1 **Dimensional Tolerance (mm):**

Protective as needed **Bevel:**

Length of Hypotenuse (mm):

35.40

Length of Legs (mm):

25.00

## Optical Properties

Angle Tolerance (arcsec):

±15

Coating:

Uncoated

Substrate:

N-BK7

Surface Quality:

40-20

Image Orientation:

Left-Handed

Ray Deviation (°):

90

Wavelength Range (nm):

350 - 2200

Power (fringes) @ 632.8nm:

1.25

Irregularity (fringes) @ 632.8nm:

0.25

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant

Certificate of Conformance:



[View](#)

## Product Details

- Ray Deviation of 90°
- Left Handed Image
- Low Arcsecond Angle Tolerance
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® High Tolerance N-BK7 Right Angle Prisms are generally used to bend image paths or redirect light at 90°. This process produces a left-handed image, depending on the prism's orientation, the image may be inverted or reverted. Right angle prisms can also be combined for image/beam displacement. TECHSPEC® High Tolerance N-BK7 Right Angle Prisms feature low arcsecond angle tolerance and are made from precision N-BK7 for use in a variety of visible light applications. These prisms are available uncoated, with a protective aluminum overcoat, or VIS° & aluminized.

## Technical Information






*Right Angle Prism Ray Path*



*Right Angle Prism Ray Path*



*Right Angle Prism Tunnel Diagram*



*Right Angle Prism Tunnel Diagram*