


[See all 17 Products in Family](#)

TECHSPEC® 25mm x 25mm Linear Polarizing Film (XP42HE-40)



Stock #71-897 [CONTACT US](#)

- 1 + S\$46⁹⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$46.90 each
Qty 11-25	S\$37.52 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Note:
Polarization axis can be identified as follows:
Circular Parts - Parallel to direction of notch on polarizer
Square Parts - Parallel to mark on protective film
Rectangular Parts - Parallel to first listed dimension

Physical & Mechanical Properties

Dimensions (mm):

25 x 25 +/- 0.3

0.40 +/- 0.05

Thickness (mm):

Polarizing Film

Construction:

Optical Properties

30,000:1 (Nominal at 555nm)

Extinction Ratio:

Polymer Film XP42HE-40

Substrate: □

Transmission (%):
Single: 42.6 (nominal @ 555nm), 41.1 (average 420-700nm)
Parallel: 36.4 (nominal @ 555nm), 34.0 (average 420-700nm)
Crossed: 0.001 (nominal @ 555nm), 0.002 (average 420-700nm)

420 - 700

Wavelength Range (nm):

>99.99% (nominal at 555nm)

Polarization Efficiency (%):

Environmental & Durability Factors

-10 to +60

Operating Temperature (°C):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

REACH 241:

Product Details

- Superior 30,000:1 Extinction Ratio
- Excellent Transmission from 420-700nm
- Available in a Range of Sizes
- Custom Sizes Available

TECHSPEC® Ultra-High Contrast Polarizing Film (XP42HE) are designed to produce a 30,000:1 contrast ratio from 420 – 700nm with an excellent transmission of 42.6%. These polarizing films are available in rectangular geometries in a range of sizes. TECHSPEC Ultra-High Contrast Polarizing Film (XP42HE) are easily cut to required geometries using common cutting tools for system integration. Additionally, the 500 x 1000mm version [#24-286](#) and [#71-907](#) are available with an adhesive backing to facilitate incorporation into various applications. These polarizing films are ideal for imaging, metrology, and microscopy applications where contrast sensitivity is paramount.