

27x27mm Half Mirror Coaxial Light White

See More by [CCS](#)



Stock #21-830 **1 In Stock**

⊖ 1 ⊕ S\$1,869⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,869.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
LFV3-G-27SW

Type of Illumination:
LED Illuminator

Manufacturer:
CCS

Geometry:
Coaxial Light

Illumination Mode:
Constant

Physical & Mechanical Properties

Dimensions (mm):
W 39 mm x D 56 mm x H 31 mm

Weight (g):
110

Active Area (mm):
27.4 mm x 27 mm

Optical Properties

Color:
White

Electrical

Power Consumption (W):
5

Hardware & Interface Connectivity

Input Voltage (V):
24

Power Supply:
Power Supply Required and Sold Separately.
USA: [#73-491](#)
Europe: [#73-491](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#73-491](#)

Environmental & Durability Factors

Color Temperature (K):
7000

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)


Product Details

- Unique Design Prevents Ghost Images
- Available in Red, White, and Blue
- Ideal for Use with High Resolution Cameras

CCS High-Resolution Coaxial Lights are designed to provide diffused lighting for high-resolution imaging of shiny, flat surfaces. Designed to prevent ghost reflections and achieve higher system resolution, these coaxial lights integrate a unique thin beamsplitter to minimize deviation through in the imaging path. CCS High-Resolution Coaxial Lights are ideal for industrial imaging applications including inspection of glossy surfaces, pattern detection on PCBs, and measuring dimensions of glass.

Technical Information

Imaging Example: Imaging Comparison of Resolution Evaluation Chart



[Imaging conditions] Camera: 2448x2048 3.45 µm monochrome camera, Lens: 2x telecentric lens, Field of view: 4.2 x 3.5 mm (the image is a sub-out of about 1.3 x 1.0 mm at the center), Resolution: 1.7 µm/pixel, WD: 110 mm, LWD: 25 mm. * The shutter speed and light intensity are adjusted for each image.