

## 28.5 x 41mm FL, Grade 1, Double-Convex Lens



Stock #75-035 CLEARANCE **4 In Stock**

S\$13<sup>93</sup>

ADD TO CART

### Volume Pricing

Qty 1+	S\$13.93 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

Diameter (mm):  
28.50

### Optical Properties

Effective Focal Length EFL (mm):  
41.00

Numerical Aperture NA:  
0.35

### Regulatory Compliance

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

20 - 29.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

