


# 3" x 3" Positive, USAF 1951 Target



UV Fused Silica and Fluorescent USAF 1951 Resolution Targets

Stock **#57-898** CLEARANCE **2 In Stock**

-

1

+

S\$639<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | S\$639.80 each                |
| Qty 5+         | S\$609.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Positive Target

Physical & Mechanical Properties

Dimensions (inches):

3 x 3

Thickness (mm):

1.00

Optical Properties

|                                                           |  |
|-----------------------------------------------------------|--|
| Coating:                                                  |  |
| Vacuum Deposited Durable Chromium                         |  |
| Substrate:                                                |  |
| UV Fused Silica (Corning 7980)                            |  |
| Optical Density OD (Average):                             |  |
| >3.0                                                      |  |
| Resolution:                                               |  |
| Minimum: Group -2, Element 1, Maximum: Group 7, Element 6 |  |
| Surface Quality:                                          |  |
| 20-10                                                     |  |
| Surface Flatness (P-V):                                   |  |
| 2λ                                                        |  |

|                             |  |
|-----------------------------|--|
| Regulatory Compliance       |  |
| RoHS 2015:                  |  |
| Compliant                   |  |
| Certificate of Conformance: |  |
| View                        |  |
| Reach 240:                  |  |
| Compliant                   |  |

## Product Details


- Designed for Calibration of UV or Fluorescence Microscopes
- Fluorescent Targets have 365nm Excitation Wavelength, 550nm Emission Wavelength
- Negative and Positive Targets Available

The Fused Silica Positive Target (chrome pattern, clear background) has the chrome pattern deposited on the top surface of the target, as does the Fused Silica Negative Target (clear pattern, chrome background).

The Fluorescent Fused Silica Targets are ideal for applications involving fluorescence and confocal microscopy, nanotechnology, photolithography, and other UV-based imaging systems. The Fluorescent Fused Silica Positive Target (chrome pattern, clear background) has a fluorescent material on the top surface of the target. The Fluorescent Fused Silica Negative Target (clear pattern, chrome background) has a fluorescent material on the bottom surface.

**Note:** Chrome coated top surface will reflect UV radiation. Avoid direct skin contact and eye exposure to UV energy. [UV protective eyewear](#) sold separately. Fluorescent material adds 0.1 - 0.2mm to thickness of fluorescent targets.

## Technical Information



| Element | Group Number |       |      |      |      |       |       |      |       |       | For High Res only |       |
|---------|--------------|-------|------|------|------|-------|-------|------|-------|-------|-------------------|-------|
|         | -2           | -1    | 0    | 1    | 2    | 3     | 4     | 5    | 6     | 7     | 8                 | 9     |
| 1       | 0.250        | 0.500 | 1.00 | 2.00 | 4.00 | 8.00  | 16.00 | 32.0 | 64.0  | 128.0 | 256.0             | 512.0 |
| 2       | 0.280        | 0.561 | 1.12 | 2.24 | 4.49 | 8.98  | 17.95 | 36.0 | 71.8  | 144.0 | 287.0             | 575.0 |
| 3       | 0.315        | 0.630 | 1.26 | 2.52 | 5.04 | 10.10 | 20.16 | 40.3 | 80.6  | 161.0 | 323.0             | 645.0 |
| 4       | 0.353        | 0.707 | 1.41 | 2.83 | 5.66 | 11.30 | 22.62 | 45.3 | 90.5  | 181.0 | 362.0             | —     |
| 5       | 0.397        | 0.793 | 1.59 | 3.17 | 6.35 | 12.70 | 25.39 | 50.8 | 102.0 | 203.0 | 406.0             | —     |
| 6       | 0.445        | 0.891 | 1.78 | 3.56 | 7.13 | 14.30 | 28.50 | 57.0 | 114.0 | 228.0 | 456.0             | —     |