

300mm, 2mm steps, Machine Vision Micrometer



EO Machine Vision Stage Micrometer

Stock **#58-293** CLEARANCE **1 In Stock**

-

1

+

\$884⁹⁰

~~\$1,769.80~~

ADD TO CART

Volume Pricing	
Qty 1-4	\$1,769.80 \$884.90 each
Qty 5+	\$1,682.72 \$841.36 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

150.00

Number of Divisions:

0.125

Line Width (mm):

2mm	Increments:
300.00	Scale Length (mm):
50.8 Wx338.1 L x6.35 T	Dimensions (mm):
±1.27	Dimensional Tolerance (mm):
±0.003	Line Width Tolerance (mm):
±0.003 up to 125mm; ±0.005 up to 300mm	Accuracy (mm):

Optical Properties

First Surface Reflective Chromium, OD > 3.0 Reflectivity = 50% ±5% @ 550nm	Coating:
Float Glass	Substrate:
40-20 Over Pattern Area	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- NIST Traceable Certificate of Accuracy Included
- Ideal for Quick Calibration of Vision Systems
- Durable Storage Case Included

The EO Machine Vision Micrometers are ideal for calibrating a variety of machine vision systems. They provide a quick means for ensuring precise measurements, whether output is direct to a monitor or image analysis software is being utilized. Featuring a precision scale over the entire 300mm length, these micrometers are ideal for large fields of view and a wide range of resolutions. The line pattern is held to tight tolerances to guarantee accuracy and repeatability. These are an ideal tool for any mid or low power video lens measurement system. For higher power systems, consider our [Microscope Image Analysis Stage Micrometers](#) or our [Multi-Function Calibration Targets](#).